collaboration tools


UNDERSTANDING COLLABORATION TOOLS	102
MOBILE MARKERBOARD CONFIGURATIONS	103
MORILE MARKERROARD RASICS	104

understanding collaboration tools

Learning and meeting environments can be used with collaboration tools that support mobility in teaching environment or group work.



Expansion Learning Tables proposes different types of the Mobile Markerboard, refer to the following page for details



mobile markerboard configurations

All Mobile Markerboard configurations are available in widths 42" or 48" and heights 66" or 72"



Non-Magnetic Glass Front (G)/ Felt Back (E)



Non-Magnetic Glass Front (G)/ Non-Magnetic Glass Back (G)









Magnetic Glass Front (M)/ Felt Back (E)



Magnetic Glass Front (M)/ Magnetic Glass Back (M)




• Felt on the backside is tackable



- Magnetic or Non-magnetic glass allows a writing surface
- Only Magnetic Glass is compatible with Rare Earth Magnets
- The glass is 5/32" (4 mm) Back-Painted tempered glass thickness


mobile markerboard basics


The Mobile Markerboard is designed to enhance collaboration in learning and meeting areas. Its unique design allows to place two markerboard side-by-side to extend writing worksurface without minimal supports into the user space.



Mobile Markerboard (XCMBM)

- Two front finish options are available: Magnetic (M) and Non-Magnetic (N) Glasses
- Comes with a variety of back finish options including Felt (E), Magnetic Glass (M) and Non-Magnetic Glass (N)
- Is **not** structural, therefore **does not** support worksurfaces
- An handle is included and can be specified Left (L) or Right (R)
- Comes with two feet for more stability
- Three casters are included:
- 1 lockable swivel caster on each foot. Casters have a 75 mm diameter
- 1 not lockable unidirectional caster, on front, underneath of the board. Caster has a 100 mm diameter.
- The casters cannot be replaced by levelers





- Integrated marker holder, drymarkers and eraser are included
- A spare Dry-Erase Kit (XCDEK) can be specified separately. Refer to the Table Accessories section for details